




NUMBER C-173852

3rd ANGLE PROJECTION

METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST



注 :

- △. [-A-] 面より2mmの範囲で測定.
- △. 相手ハウジングと所定の機能を満足して嵌合できること.
- 3. 内装するリセプタクルコネクタ型番173630, 173631.

NOTE:

- △. MUST BE KEPT BETWEEN [-A-] AND 2.
- △. TO BE MATED WITH THE CAP HSG SMOOTHLY.
- 3. APPLIED RECEPTACLE CONTACT P/N, 173630, 173631.

色 (COLOR)	名称 (NAME)	型番 (P/N)
WHITE 白	14Pos. PLUG HOUSING 14極 プラグハウジング	1-173852-1
YELLOW 黄		173852-7
GRAY 灰		173852-6
BLUE 青		173852-5
GREEN 緑		173852-4
BLACK 黒		173852-2
WHITE 白	14Pos. PLUG HOUSING 14極 プラグハウジング	173852-1

LTR	REVISION RECORD	DR	CHK	DATE
D1	OBSOLETE 1- -1 FJ00-0279-99	AY	KB	29FEB 90
D	ADDED COLOR ITEM 色追加 FJ00-0854-94	HK	KA	6/30 '94
C	REDRAWN & ADDED COLOR ITEM 再作成&色追加 J-0114	YF	AT	5/28 '91

Copyright ©1988年 AMP (Japan) LTD. ALL RIGHTS RESERVED.	Copyright ©1988 AMP (Japan) LTD. ALL RIGHTS RESERVED.
WIRE RANGE mm* (AWG - )	INSULATION DIA mmφ
MATERIAL PBT	FINISH
DR. Y. Fujimori 5/28 '91	DE.
CHK.	APP. A. TOMITA 5/28 '91

NAME .070 SRS MLC 14Pos. PLUG HSG .070 シリーズ マルチロック コネクタ 14極 プラグハウジング			
GENERAL TOLERANCE	SIZE	LOC	NUMBER
0<≦10 : ±0.2 10<≦30 : ±0.25 30<≦100 : ±0.3 ANGLES : ±3°	A3	J	C-173852
SCALE	REV.	SHEET	
2-1	D1	##	