# **Specialty Plates**



- IFP18OW is the only Duplex opening plate in the industry that is UL listed for power and low-voltage with label fields.
- 106 frames fit industry standard duplex style openings.

# Features/Benefits

- Instant communication mounting capabilities within a duplex electrical design.
- Frames deliver 2- to 6-port configurations, lending flexibility and increased capacity to the work area.

### **Specifications**

High-impact polymer construction.





# **Duplex and IFP Cover Plates**

	Duplex	Duplex	IFP Duplex w/Label Fields
Color/Finish	Single-Gang	Double-Gang	Single-Gang
Black	NP8BK	NP82BK	-
Brass	SB8	SB82	-
Electric Ivory	NP8EI	NP82EI	-
Gray	NP8GY	NP82GY	-
Light Almond	NP8LA	NP82LA	-
Office White	-	-	IFP18OW
Stainless Steel	SS8	SS82	-
White	NP8W	NP82W	-
		·	





# **Duplex Wall Plates**

#### Standard Nylon

Didiidala, Hylon					
Ports	1-Gang	2-Gang	3-Gang	4-Gang	
See Color Code	NP8XX	NP82XX	NP83XX	NP84XX	
on Page 30					

# Mid-Size, Nylon

Ports	1-Gang	2-Gang
See Color Code	NPJ8XX	NPJ82XX
on Page 30		



# **Duplex 106 Outlet Frames**

	2-port	4-port
Black	BR106B 100G	Q106B V10G
Electric Ivory	BR106E 10G	Q106E V10G
Gray	BR106G 10G	Q106G 10G
Office White		Q1060 V10G
White	BR106W 10G	Q106W 10G





### **Box Eliminator**

Description	Catalog No.
Single-gang box eliminator used in place of an electrical box, inserts into, and secures to a drywall opening providing a means to mount a single-gang plate.	BRBE1
Double-gang box eliminator used in place of an electrical box, inserts into, and secures to a drywall opening providing a means to mount a double-gang plate.	BRBE2



BRBE2

#### **630 Wall Mount Phone Plates**

Designed for use with wall mount telephones. Provides corrosion-resistance, durability and will mount to any standard single-gang box. Available in a flat, flush-mount or recess style.

Stainless Steel,	Single-gang wall phone plate	
Jack Format	Includes	Catalog No.
Flush	6-position USOC gray jack, RJ25	P630S1GJ6
Flush	8-position Category 5e, gray jack, RJ45	P630S1GJ8
Flush	8-position Category 6, gray jack, RJ45	P630S1GC6
Flush	8-position 10GbE, gray jack, RJ45	P630S1GJ10G 10G
Recessed	6-position USOC gray jack, RJ25	P630SR1GJ6
Recessed	8-position Category 5e, gray jack, RJ45	P630SR1GJ8
Recessed	8-position Category 6, gray jack, RJ45	P630SR1GC6
Recessed	8-position 10GbE, gray jack, RJ45	P630SR1GJ10G 10G



