

6

5

4

3




2

1

Rev	AWO #	Description	Date	Appr
-	9427	RELEASED	3/20/09	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Phosphor Bronze, Tin plated

Electrical:

Operation voltage: 125 VAC max

Current rating: 4 Amps max per Pole

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min @ DC500V

Dielectric withstanding voltage: 1250 VAC for 1 minute

Mechanical:

Wire Range: 20 to 28 Awg

Environmental:

Operating temperature: -30°C to +105°C

Lead free, RoHS compliant.

Recommended soldering temp: 235°C for 5 sec.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: TERMINAL BLOCK, SPRING FOR PLUGGABLE,
3.81MM PITCH

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM TOLERANCES: EXCEPT AS NOTED INCHES		HOLE SIZE	
.X	± .10	ØXX	± .10
.XX	± .020	ØXXX	± .015
.XXX	± .015	ØXXXX	± .010
APPROVALS	DATE		
DRAWN	DY	3/20/09	
CHECKED			
APPROVED			
SIZE	PART NO.	REV.	
X	EB2-XX-M-B	-	
REF:	S00007T	SCALE:	NTS
		SHEET	1 OF 1

6

5

4

3

2

1