

Plier Wrench, insulated patented

86 07 250



- Plier and Wrench in a single tool
- excellent for gripping, holding, pressing and bending workpieces
- zero backlash jaw surface pressure prevents damage to edges of sensitive nuts (Cu)
- with scale for presetting apart from the workpiece
- no unintentional shift of the gripping jaws and no slipping of the joint
-
- parallel jaws allow infinitely variable gripping of all widths to the specified maximum size
- the action of the jaws allows screwed connections to be tightened and released quickly using the ratchet principle
- lever transmission greater than 10 - 1 for strong gripping power



Warning! Please do strictly observe operation instructions!

Article- No.	EAN 4003773-	Head	Handles	B1 mm	B2 mm	B3 mm	Working capacities Inch	Working capacities mm	Length mm	g
86 07 250	065067	nickel plated	plastic dipped insulated, VDE-tested	8,0	8,0	14,0	1 3/4	to 46	250	660

technical change and errors excepted