

SMX Series



- SMX-01
- SMX-06
- SMX-12Y

- High SPL
- Through Hole Design
- Top Sound Hole
- Dip Solderable and Washable

Specifications:

	SMX-01	SMX-06	SMX-12
SPL	Min. 80 dB Typ. 84 dB	Min. 85 dB Typ. 89 dB	
Rated Voltage	1.5 V _{p-p}	6 V _{p-p}	12 V _{p-p}
Rated Frequency	2,048 Hz		
Mean Current Consumption	Max 40 mA		
Operation Temp.	-30°C to +80°C	-40°C to +85°C	
External Size	14 x 18 x 11 mm		
Mass	3.5g		

