



P/N	MATERIAL / COLOR
94090 - 4180	NYLON 6.6 V2 NATURAL
94090 - 4184	NYLON 6.6 GWT 750°C sec.IEC 60335-1 TEST METHOD IEC 60695-2-11 NATURAL

PACKAGING: 2.500 pcs in nylon bag
in carton box. S.P.Q.

Std. Descr. "HSG FOR 6.3 TYPE FEMALE TERM 6 WAY"

REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRAWN BY	DATE	TITLE
			mm	INCH			
		$\nabla = 0$	4 PLACES \pm ---	\pm ---			6 WAY HOUSING FOR 6.3 TYPE FEMALE TERMINALS
		$\nabla = 0$	3 PLACES \pm ---	\pm ---			
			2 PLACES ± 0.1	\pm ---			
			1 PLACE ± 0.2	\pm ---			
			ANGULAR $\pm 2^\circ$				MOLEX INCORPORATED
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				
			SEE TABLE				SD-94090-021