

MAA-03A-L60-B



- Back Electret Condenser Microphone
- Omni-directional
- 2 capacitors inside for low noise
- 60 mm wire leads

Specifications:

Sensitivity	-44 ± 3 dB
Rated Voltage	2.0 V
Operating Voltage	1.0-10.0 V
Current Consumption	500 μ A (max)
S/N Ratio	55 dB (min)
Directivity	Omni
Operation Temp.	-30°C to +70°C
External Size	$\phi 3\text{mm} \times 1.5\text{mm}$
Mass	<0.5 g

Circuit Diagram

