

ADAM-6022

ADAM-6024

Ethernet-based Dual-loop PID Controller

12-ch Isolated Universal Input/Output

Modbus TCP Module



ADAM-6022



Specifications

General

- **Loop Number** 2 (3 AI, 1 AO, 1 DI, 1 DO for each control loop)

Analog Input

- **Channels** 6 (differential)
- **Input Range** $\pm 10 V_{DC}$, 0 ~ 20 mA, 4 ~ 20 mA

Analog Output

- **Channels** 2
- **Output Type** V, mA
- **Output Range** 0 ~ 10 V_{DC} , 4 ~ 20 mA, 0 ~ 20 mA

Digital Input

- **Channels** 2
- **Dry Contact** Logic level 0: close to GND
Logic level 1: open
- **Wet Contact** Logic level 0: 0 ~ 3 V_{DC}
Logic level 1: 10 ~ 30 V_{DC}

Digital Output

- **Channels** 2, open collector to 30 V, 100 mA max. load
- **Power Dissipation** 300 mW for each module

Ordering Information

- **ADAM-6022** Ethernet-based Dual-loop PID Controller



ADAM-6024



Specifications

Analog Input

- **Channels** 6 (differential)
- **Input Range** $\pm 10 V_{DC}$, 0 ~ 20 mA, 4 ~ 20 mA

Analog Output

- **Channels** 2
- **Output Type** V, mA
- **Output Range** 0 ~ 10 V_{DC} , 4 ~ 20 mA, 0 ~ 20 mA

Digital Input

- **Channels** 2
- **Dry Contact** Logic level 0: close to GND
Logic level 1: open
- **Wet Contact** Logic level 0: 0 ~ 3 V_{DC}
Logic level 1: 10 ~ 30 V_{DC}

Digital Output

- **Channels** 2, open collector to 30 V, 100 mA max. load
- **Power Dissipation** 300 mW for each module

Supports

- **Peer-to-Peer (Receiver only)**
- **GCL (Receiver only)**

Ordering Information

- **ADAM-6024** 12-ch Isolated Universal I/O Modbus TCP Module

19	Embedded Controllers
20	PC-based Controllers
21	PAC
22	Motion Control
23	RS-485 I/O
24	Ethernet I/O
25	Building Automation
26	Self-service Terminals
27	eHome Platforms

Common Specifications	
General	
▪ LAN	10/100Base-T(X)
▪ Power Consumption	4 W @ 24 V_{DC}
▪ Connectors	1 x RJ-45 (LAN), Plug-in screw terminal block (I/O and power)
▪ Watchdog	System (1.6 second) and Communication (programmable)
▪ Power Input	10 ~ 30 V_{DC}
▪ Supports Modbus/TCP, TCP/IP, UDP and HTTP Protocols	
Analog Input	
▪ Input Impedance	20 M Ω
▪ Accuracy	$\pm 0.1\%$ of FSR
▪ Resolution	16-bit
▪ Sampling Rate	10 sample/second
▪ CMR @ 50/60 Hz	90 dB
▪ NMR @ 50/60 Hz	60 dB
▪ Span Drift	± 25 ppm/ $^{\circ}$ C
▪ Zero Drift	± 6 μ V/ $^{\circ}$ C
Analog Output	
▪ Accuracy	$\pm 0.1\%$ of FSR
▪ Resolution	12-bit
▪ Drift	± 50 ppm/ $^{\circ}$ C
▪ Current Load Resistor	0 ~ 500 Ω
Protection	
▪ Isolation Protection	2,000 V_{DC}
▪ Built-in TVS/ESD Protection	
▪ Over Voltage Protection	$\pm 35 V_{DC}$
▪ Power Reversal Protection	
Environment	
▪ Operating Temperature	-10 ~ 50 $^{\circ}$ C (14 ~ 122 $^{\circ}$ F)
▪ Storage Temperature	-20 ~ 80 $^{\circ}$ C (-4 ~ 176 $^{\circ}$ F)
▪ Operating Humidity	20 ~ 95% RH (non-condensing)
▪ Storage Humidity	0 ~ 95% RH (non-condensing)