



Rev	AWO #	Description	Date	Appr
-		RELEASED	10/22/09	

APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_



Poles: 2 thru 24  
 A = .150 [3.81] x No. of (Poles - 1) + .193 [4.90]  
 B = .150 [3.81] x No. of (Poles - 1)  
 C = .150 [3.81] x No. of (Poles - 1) + .205 [5.20]

**ADAM TECH**

909 Railway Avenue, Union, NJ 07083  
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: .150 [3.81] TERMINAL BLOCK

**SPECIFICATIONS:**  
 Material: Insulator: Thermoplastic, rated UL 94V-0  
 Insulator color: Green  
 Contact: Brass, Tin plated  
 Electrical: Operating voltage: 300 VAC max  
 Current rating: 10 Amps max  
 Withstanding voltage: 1.6kV  
 Environmental: Operating temperature: -30°C to +105°C  
 Lead free, RoHS compliant.  
 Recommended soldering temp: 235°C for 5 sec.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]		TOLERANCES: EXCEPT AS NOTED	
INCHES		HOLDS	
.X	± .10	ØX	± .10
.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010
APPROVALS		DATE	
DRAWN	DY	10/22/09	
CHECKED			
APPROVED			
SIZE	PART NO.	REV.	
X	EB3-XX-B	-	
REF:	S00007T	SCALE:	NTS
SHEET 1 OF 1		SHEET 1 OF 1	