



Specifications

1. Rated Voltage.....6 VDC
2. Operating Voltage.....3~18 VDC
3. Max. Rated Current.....5mA at 6 VDC
4. Min. Sound Pressure Level.....80dB at 6VDC/30cm
5. Resonant Frequency.....4.0±0.5KHz
6. Tone Nature.....Continuous
7. Case Material.....ABS
8. Operating Temperature.....-20~+60°C
9. Store Temperature.....-30~+70°C
10. Weight.....2g

				KEPO KEPO ELECTRONIC CO., LTD. http://www.kepo.com.tw	
				KPR3-2313	
No.	DESCRIPTION	APPROVED	DATE		
TOLERANCES UNLESS NOTED OTHERWISE X = .XX = .XXX = 90° FORMED +2° ANGLES -1°		APPROVALS	DATE	UNIT	DWG NO.
FIRST ANGLE PROJECTION		CHECKED		mm	KP3.840.312
		APPROVED	03.04.23	SCALE	SHEET
				NOT TO SCALE	VER 1.1