RockStar® Housings IP65 / NEMA Type 4X

Side locking, upper side

Size 10


Hood

Hood, Cable Entry sideways



а	Version	Cover	b (mm)	Designation	Order No.
M32	with thread	Cover	79	HDC 32B TSBO 1M32G	1788410000






Base

Bulkhead housing



Version	Cover	b (mm)	Designation	Order No.
	with cover	55	HDC 32B ADBO	1218800000



End locking, lower side


Size 12

Hood

Hood, Cable Entry sideways




а	Version	Cover	b (mm)	Designation	Order No.
M32	with thread		94	HDC 48B TSLU 1M32G	1788320000
M40	with thread		94	HDC 48B TSLU 1M40G	1788310000
M50	with thread		94	HDC 48B TSLU 1M50G	1788300000
PG 29	with thread		94	HDC 48B TSLU 1PG29G	1650850000
PG 36	with thread		94	HDC 48B TSLU 1PG36G	1650860000
PG 42	with thread		94	HDC 48B TSLU 1PG42G	1670470000



Hood, Cable Entry at top



а	Version	Cover	b (mm)	Designation	Order No.
M32	with thread		94	HDC 48B TOLU 1M32G	1788350000
M50	with thread		94	HDC 48B TOLU 1M50G	1788330000
PG 29	with thread		94	HDC 48B TOLU 1PG29G	1650980000
PG 36	with thread		94	HDC 48B TOLU 1PG36G	1651000000




Base

Bulkhead housing



Vers	ion Cover	b (mm)	Designation	Order No.
	with cov	er 62	HDC 48B ADLU	1222900000



Base housing



а	Version	Cover b	(mm)	Designation	Order No.
M32	with thread	without cover	100	HDC 48B SLU 1M32G	1904190000
M32	with thread	with cover	120	HDC 48B SDLU 1M32G	1904150000
M32	with thread	without cover	100	HDC 48B SLU 2M32G	1788370000
M32	with thread	with cover	120	HDC 48B SDLU 2M32G	1788390000
M40	with thread	without cover	100	HDC 48B SLU 2M40G	1788360000
PG 29	with thread	without cover	100	HDC 48B SLU 1PG29G	1651100000
PG 29	with thread	with cover	120	HDC 48B SDLU 1PG29G	1799810000
PG 29	with thread	with cover	120	HDC 48B SDLU 2PG29G	1667560000

