

RED INDICATES ORIGINAL

DATA CONTAINED IN THIS DOCUMENT IS
 PROPRIETARY TO TROMPETER ELECTRONICS INC.
 AND SHALL NOT BE DISCLOSED, COPIED OR USED
 FOR PROCUREMENT OR MANUFACTURE WITHOUT
 EXPRESS WRITTEN PERMISSION OF TROMPETER
 ELECTRONICS INC.


REVISIONS

010-0055

SH 1C

REV	DESCRIPTION	DATE	APPROVED
K	REVISED PER ECO #13819	2/15/01	<i>[Signature]</i>

DASH NO	MARKING
BASIC	W/MARKING
-U	W/O MARKING



BASIC SHOWN

3. RECOMMENDED GAUGING OF INDENTERS IN FULLY CLOSED CONDITION: .026 MIN, .031 MAX DIA

△ OPEN HANDLE SPAN 4.20

1. FINISH: HAND GRIP: RED
 FRAME ASSY: BLACK OXIDE COATED CRS

INTERPRET DRAWING PER MIL-STD-100 DIMENSIONS ARE IN INCHES AND INCLUDE FINISH THICKNESS UNLESS OTHERWISE SPECIFIED		TOL: UNLESS SPECIFIED .XX .XXX .XXXX .XXXXX ANGLES			
DRAWN DKC	DATE 2-8-01	MATERIAL:			
CHECKED <i>[Signature]</i>	DATE 2/14/01	FINISH: SEE NOTE: 1		TITLE: 8 POINT CRIMP TOOL 75 OHM PIN CENTER CONTACTS	
APPROVED <i>[Signature]</i>	DATE 2-15-01	SIZE A	CAGE CODE 14949	DRAWING NO. 010-0055	REV. K
NEXT ASSY		SCALE 1/1	DATE: 8-26-88	SHEET 1C	