


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART, CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.


SPC-F006.DWG

REVISIONS				DOC. NO. SPC-F006 * Effective 7/8/02 * DCP No 1308			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECK'D	DATE	APPR'D
1488	A	RELEASED	JWM	1/17/03	HQ	1/23/03	DJC
2035	B	Dimension Correction	JN	4/1/08	JN	4/1/08	JN



- Test probe set includes
 - 2 probes with 2mm tip to right angle sheathed 4mm banana plugs, 18AWG PVC wire, Black and Red
 - 2 insulated alligator clips, Black and Red
- Specifications
 - Probe:
 - Wire: 18AWG Stranded copper, PVC (-20°C ~ 80°C) 0.144 ±0.008 [3.6 ±0.2] O.D.
 - Probe and Plug Bodies: Flexible PVC (Grey) over hard PVC core (color matches wire), UL94V-0
 - Tip: Brass, nickel plated
 - Plug Contact: 4mm, Leaf-phosphor bronze
 - Plug body: Brass, nickel plated
 - Clip:
 - Body: Brass, nickel plated
 - Contact: 2mm socket, phosphor bronze, gold plated
 - Boot: Flexible PVC (color matches wire)
 - Rating:
 - IEC61010-2031 at 1000V CAT III P2
 - Current: 10A Max.
 - Temperature: -25°C ~ 80°C

Probe and alligator clip assembled



DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.				TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.			
DRAWN BY:		DATE:		DRAWING TITLE:			
Jeff McVicker		1/17/03		DMM Probe Set			
CHECKED BY:		DATE:		SIZE		DWG. NO.	
Hiham Odish		1/23/03		A		76-108A	
APPROVED BY:		DATE:		SCALE:		NTS	
Daniel Carey		1/23/03		U.O.M.: INCHES [mm]		SHEET: 1 OF 1	