


1 2 3 4 5 6 7 8 9 10

MOLD	INSIDE NO.	OUTSIDE NO.
DB25P MALE	960109-1	960109-1

機密等級: [ ] 極機密 [V] 機密 [ ] 一般文件



J1	PIN OUT	J2
1	_____	1
2	_____	2
3	_____	3
4	_____	4
5	_____	5
6	_____	6
7	_____	7
8	_____	8
11	_____	11
15	_____	15
17	_____	17
18	_____	18
20	_____	20
22	_____	22
23	_____	23
25	_____	25
SHELL	_____	SHELL

NOTES:

1. WIRE: NON-UL 28AWG 18C+1 AL/MY OD=6.0MM  
JACKET COLOR: IVORY
2. CONN: J1,J2-DB25P MALE MOLDED TYPE W/TS
3. SCREW: 4\*30.5MM(#4-40UNC)
4. INSIDE: MOLDING
5. OUTSIDE MOLD PVC COLOR: IVORY
6. PACKING: W/CLEAR POLYBAG

G.W. NO	LENGTH
2CB155200000000	2M±0.05M
2CB155500000000	5M±0.05M
2CB155300000002	3M±0.05M

REV	DESCRIPTION	DATE	ECN NO.
1-3	變更線材芯數	AUG-18-2004	工程修正
1-2	ADD ITEM/MODIFY G.W NO	FEB-16-2004	

DWG NAME: RS232 MODEM CABLE	
G. W. NO: SEE THE TABLE	CUS. ID:
CUS. NO:	DWG. NO: DB25P CABLE-A10
SHEET: 1/1	TOLERANCE: . X _____ . XX ±0.40
	SCALE: 1:1
	UNIT: mm
DRAW. BY:	CHECKED
APPROVE	