
SPECIFICATIONS

Model Number: CD24B3 Part Number: 031573





Mechanical Drawing:



Motor:

Nominal Voltage = 24 vdcOperating Voltage Range = 12 - 28 vdcNominal Running Current = 1.20 ampsLocked Rotor Current = 3.00 amps**Running Power** = 29.0 watts Average Speed = 1650 rpm**Bearings** = BallAir Flow = 550 cfmNoise = 49.1 dBA

Construction:

Venturi: Die-Cast Aluminum, Black Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 60,000

hours at 40°C.

Additional Features:

Brushless DC Motor Polarity Protected Locked Rotor Protection Automatic Restart Capability

Operating Temperature: -10°C to 70°C Storage Temperature: -40°C to 85°C

Termination:

12" Lead wires, 22 AWG, UL 1061

Red = Power (+) Black = Return (-)

Agency Approvals:

UL, CUR, TUV, CE