



LEGEND

2107- \* \* \* \* \*

FORM  
1=CHAIN  
2=LOOSE

BARREL I.D.

WIRE GAGE  
5=18-24 AWG  
6=24-30 AWG



NOTES:

1. MATERIALS:

FINISHES:

B= (P901) HOT TIN DIP .000020/(0.0005) MIN.

C= (P535) SELECT GOLD PLATE .000015/(0.00038) MIN. IN CONTACT AREA OVER .000030/(0.00076) MIN. NICKEL OVERALL.

D= (P562) SELECT GOLD PLATE .000020/(0.0005) MIN. IN CONTACT AREA OVER .000030/(0.00076) MIN. NICKEL OVERALL.

G= (P550) SELECT GOLD PLATE .000015/(0.00038) MIN. IN CONTACT AREA OVER .000030/(0.00076) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH OVERALL.

5. THESE TERMINALS FOR USE WITH .045/(1.14) ROUND AND SQUARE PINS.  
6. THESE TERMINALS WILL ACCEPT STRANDED WIRE WITH .031/(0.79) MAX. THICK INSULATION.  
7. A 2° MAX. ANGLE IS ALLOWED.

THESE TERM'S. MATE WITH (1.14)/.045 ROUND PIN

PART NO.	ENG. NO.	OLD ENG. NO.
02-05-1116	2107-1B6N1	2107-T
02-05-1117	2107-1B6N2	2107-TL
02-05-1104	2107-1B5N1	1129-T
02-05-1105	2107-1B5N2	1129-TL
02-05-1205	2107-2A5N2	2123-L
02-05-1204	2107-2B5N1	2123-T
02-05-1205	2107-2B5N2	2123-TL
02-05-1216	2107-2B6N1	
02-05-1217	2107-2B	

THESE TERM'S. MATE WITH (1.14)/.045 SQUARE PIN

PART NO.	ENG. NO.	OLD ENG. NO.
02-05-1115	2107-1B6P1	2107-1(P901)
	2107-1B6P2	2107-1(P901)L
	2107-1B5P1	
	2107-1B5P2	
	2107-1D5P1	
	2107-1D5P2	
	2107-1G5P1	
	2107-1G5P2	
	2107-1D6P1	
	2107-1D6P2	
	2107-2A6P1	
	2107-2A6P2	
	2107-2A5P1	
	2107-2A5P2	
	2107-2B5P1	
	2107-2B5P2	
	2107-2C5P1	
	2107-2C5P2	