

ADD PANEL DIMS.  
LCP2004-0895

|    |     |     |                |                         |
|----|-----|-----|----------------|-------------------------|
| 0  | --- | 005 | JBS            | 06/10/03                |
| 13 | 01  | --- | BW             | 06/13/03                |
| 0  | --- | --- | BW             | 06/16/03                |
|    | .5  |     | SD1772-36*.DGN | SEE CHART SD-1772-36*** |

2 : 1 X

X


.062/(1.57) HOUSING,  
PLUG AND RECEPTACLE,  
36 - CIRCUIT

|   |   |
|---|---|
| 2 | G |
| 1 | G |




| PLUG       |              |
|------------|--------------|
| PART NO.   | ENG. NO.     |
| 03-06-2361 | 1772-36P     |
| 03-06-2362 | 1772-36P-1   |
| 03-06-7361 | 1772-36P-D   |
| 03-06-7362 | 1772-36P-1-D |
|            |              |
|            |              |

| RECEPTACLE |              |
|------------|--------------|
| PART NO.   | ENG. NO.     |
| 03-06-1361 | 1772-36R     |
| 03-06-1362 | 1772-36R-1   |
| 03-06-6361 | 1772-36R-D   |
| 03-06-6362 | 1772-36R-1-D |
|            |              |
|            |              |

**PLUG LEGEND:**



**RECEPTACLE LEGEND:**




| HOUSING    | DIM. "A"      | DIM. "B"     |
|------------|---------------|--------------|
| PLUG       | 1.795/(45.59) | .825/(20.96) |
| RECEPTACLE | 1.677/(42.60) | .707/(17.96) |

RECOMMENDED PANEL OPENING

\* MAX. PANEL THICKNESS IS .060.

NOTES:

1. MATERIAL: PA 66, UL 94V-2; COLOR: NATURAL.
2. FINISH: NONE.
3. PRODUCT SPECIFICATION: NONE.
4. PACKAGING SPECIFICATION: NONE.
5. FOR USE WITH .062 SERIES TERMINALS.



**MOUNTING EAR DETAIL**

(SCALE 4:1)

|                                                         |            |            |           |                                                                        |  |                           |  |
|---------------------------------------------------------|------------|------------|-----------|------------------------------------------------------------------------|--|---------------------------|--|
| DIMENSIONS SHOWN (METRIC) INCH                          |            | ▽ = 0      |           | ▼ = 2                                                                  |  | REVISE ONLY ON CAD SYSTEM |  |
| UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR $\pm 10$ |            | INCH       |           | METRIC                                                                 |  | TITLE                     |  |
| 3 PLACE                                                 | $\pm .005$ | ---        | ---       | .062/(1.57) HOUSING,<br>PLUG AND RECEPTACLE,<br>36 CIRCUIT             |  |                           |  |
| 2 PLACE                                                 | $\pm .01$  | $\pm 0.13$ | ---       | SEE CHART                                                              |  |                           |  |
| 1 PLACE                                                 | ---        | $\pm 0.25$ | ---       | MOLEX INCORPORATED SHEET NO. DATE<br>L15LEJLL. 60532 U.S.A. 2 06/10/03 |  |                           |  |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS    |            | PART NO.   |           | DRWG. NO.                                                              |  | SIZE                      |  |
| DRG. BY                                                 | JBS        | CHK'D. BY  | BW        | SEE CHART                                                              |  | SD-1772-36-**-*           |  |
| APP'D. BY                                               | BW         | SCALE      | 2 : 1     | FILE NAME                                                              |  | DIV.                      |  |
| LTR.                                                    | REVISIONS  | LTR.       | REVISIONS | SD 1772-36 DGN                                                         |  | CP C                      |  |