



SPECIFICATION

- 1. Rated Voltage 12VDC
- 2. Operating Voltage 8~15VDC
- 3. Max. Rated Current 30mA/12VDC
- 4. Min. Sound Pressure Level 85dB/10cm
- 5. Resonant Frequency 2300 ± 500 Hz
- 6. Response Time 50ms
- 7. Case Material PBT
- 8. Operating Temperature $-20 \sim +70^\circ\text{C}$
- 9. Store Temperature $-30 \sim +80^\circ\text{C}$
- 10. Weight 2g

				KEPO KEPO ELECTRONIC CO., LTD. http://www.kepo.com.tw	
				Magnetic Buzzer	
				KPX-1212UB	
No.	DESCRIPTION	APPROVED	DATE		
TOLERANCES UNLESS NOTED OTHERWISE		APPROVALS		DATE	
.X . =		DRAWN		UNIT	
.XX . =		CHECKED		mm	
.XXX . =		APPROVED		DWG NO. KP3.840.695	
90° FORMED -2°				SCALE NOT TO SCALE	
ANGLES -1°				SHEET	
FIRST ANGLE PROJECTION				VER 1.2	