

98 Standard Tool Case, 26 parts

with safety tools

1000 V
IEC 60900
DIN EN 60900

- ▶ shock-resistant plastic case
- ▶ containing a range of conventional KNIPEX safety tools, tested according to DIN EN/IEC 60900

Article-No.	EAN-Code	Contents Article-No.	Description	Length/Size
4003773-				
98 99 12	026631	03 07 200	Combination Plier	200 mm
		70 07 160	Diagonal Cutter	160 mm
		98 00 10	Open End Wrench	SW 10 mm
		98 00 11	Open End Wrench	SW 11 mm
		98 00 12	Open End Wrench	SW 12 mm
		98 00 13	Open End Wrench	SW 13 mm
		98 00 14	Open End Wrench	SW 14 mm
		98 00 17	Open End Wrench	SW 17 mm
		98 00 19	Open End Wrench	SW 19 mm
		98 20 28	Screwdriver, for slotted screws	2.8 mm
		98 20 35	Screwdriver, for slotted screws	3.5 mm
		98 20 40	Screwdriver, for slotted screws	4.0 mm
		98 20 55	Screwdriver, for slotted screws	5.5 mm
		98 24 00	Screwdriver, Phillips	00
		98 24 01	Screwdriver, Phillips	01
		98 24 02	Screwdriver, Phillips	02
		98 40	T-Handle Drive	200 mm
		98 47 10	Hexagon Socket	SW 10 mm
		98 47 11	Hexagon Socket	$\frac{1}{2}$ Drive SW 11 mm
		98 47 12	Hexagon Socket	SW 12 mm
		98 47 13	Hexagon Socket	SW 13 mm
		98 47 14	Hexagon Socket	SW 14 mm
		98 47 17	Hexagon Socket	SW 17 mm
		98 47 19	Hexagon Socket	SW 19 mm
		98 52	Cable Knife	180 mm
		98 53 03	Dismantling Knife	155 mm



98 99 12

98 Tool Roll, 15 parts

with safety tools

1000 V
IEC 60900
DIN EN 60900

- ▶ containing a range of conventional KNIPEX safety tools, tested according to DIN EN/IEC 60900
- ▶ hard-wearing polyester fabric
- ▶ with practical, adjustable quick-release fastener

Article-No.	EAN-Code	Contents Article-No.	Description	Length/Size
4003773-				
98 99 13	026648	03 07 200	Combination Plier	200 mm
		11 17 160	Wire Stripper	160 mm
		26 17 200	Snipe Nose Side Cutting Plier	200 mm
		70 07 160	Diagonal Cutter	160 mm
		95 06 230	Cabel Shears	230 mm
		98 00 10	Open End Wrench	SW 10 mm
		98 00 13	Open End Wrench	SW 13 mm
		98 00 14	Open End Wrench	SW 14 mm
		98 00 17	Open End Wrench	SW 17 mm
		98 00 19	Open End Wrench	SW 19 mm
		98 20 28	Screwdriver	2.8 mm
		98 20 40	Screwdriver	4.0 mm
		98 20 55	Screwdriver	5.5 mm
		98 20 65	Screwdriver	6.5 mm
		98 52	Cable Knife	180 mm



98 99 13