

IDXPERT™ Handheld Labeler



**Two printer keyboard layouts.
Identical functionality and supplies.**

IDXPERT Labeling System

Part Number	Description
XPRT-ABC	IDXPERT Printer – ABC Layout*
XPRT-KEY	IDXPERT Printer – KEYBOARD Layout*

* Printer ships with: Hard carry case, 1,500' x 30' Continuous Tape, PC Cable for upgrades only, Product CD with Tutorials.

► ACCESSORIES

IDXPERT Labeling System Accessories

Part Number	Description
XPRT-AC	AC Adapter (for ABC or KEY printers)
PCCABLE-1	PC Cable for Upgrades Only (for ABC or KEY)
PCK-4	Cleaning Kit
XPRT-HC-ABC	Spare Hard Case for ABC Layout Printer
XPRT-HC-KEY	Spare Hard Case for KEYBOARD Layout Printer

► SPECIFICATIONS

Print method	Thermal transfer (non smearing)
Weight	2.4 lbs ABC / 2.15 lbs keyboard
Dimensions (L x W x H)	Keyboard layout: 9.500" x 3.500" x 7.500" (241.30 mm x 88.90 mm x 190.50 mm) ABC layout: 5.000" x 3.750" x 11.500" (127.00 mm x 95.25 mm x 292.10 mm)
Power source	6 AAs or optional AC adapter
Operating temperature	40 - 120°F (4° - 49°C)
Agency approvals	FCC Class A Approved

More Options. More Brains. More Brawn. Less Waste.

Here is the newest 300 dpi thermal, handheld labeling system that has everything it takes to make you an Identification Expert!. Label patch panels, outlet faceplates and cables. Identify racks, bays, frames, public network and data centers all with one versatile tool. The IDXPERT is the first handheld cartridge based labeling system that can print die-cut labels, self-laminating labels and sleeves as well as continuous tapes...You name it IDXPERT prints it!

Choose from two keyboard layouts, then select from a wide range of label materials engineered just for your application. That includes wire and cable markers; panel, rack and frame ID; facilities labels; and specialty labels for labs and work spaces.

More Types of Labels

- Colored continuous tapes for pipe markers, equipment ID and safety warnings
- PermaSleeve™ wire marker sleeves
- Self-laminating wire and cable markers
- Terminal block markers
- Patch panel markers
- Face plate and outlet markers
- General-purpose die-cut labels

More Sizes

- Prints from 0.06" up to 1.25" characters on label stock up to 1.5" wide

More Symbols

- Code 39 bar codes
- 82 Symbols including electrical, voice/data, safety and protection, warning, and machine and operational

More Brains

- Drop Lock & Go™ Smart Cartridges™ are fast to install and remove
- Electronically pre-calibrated to orient the label just the way you need it with no special keys to press
- Memory to store frequently used set-ups
- Ergonomic design really fits your hand
- 300 dpi thermal transfer printing stays crisp and bright

More Brawn

- Users of dot-matrix printers will benefit from crisp, non-smearing thermal transfer print quality, faster print speed and more text-editing and symbols capabilities
- Larger, more informative display
- Rugged, drop-tested construction

Less Waste

- Edge-to-edge printing on continuous tapes so you don't pay for unused label material
- Die-cut labels are pre-cut to the size you need—no waste
- Runs on 6 AAs or optional AC adapter