## **Ticket Holders**



- Ideal for identifying locations on shelving and pallet racking
- Pull-forward front allows easy loading and updates of information
- Barcodes can be scanned without removing the insert
- Pre-cut sizes from stock
- Special sizes on request up to 3M lengths

With a choice of 4 heights this clear PVC strip is supplied with either an aggressive adhesive backing for permanent locations, or with a magnetic option which offers the flexibility to change locations and is suitable for cold storage applications.


## Self-adhesive Ticket Holders

Ref	Size (H x W)	Pack	White Card Included
TS210	25mm x 100mm	100	J
TS220	25mm x 200mm	50	1
TS25/10	25mm x 1M	10	1
TS25/20	25mm x 2M	10	·
TS25/60	25mm x 2M	30	
TS25/100	25mm x 2M	50	
TS25/250	25mm x 2M	125	
TS310	38mm x 100mm	100	1
TS320	38mm x 200mm	50	1
TS38/10	38mm x 1M	10	1
TS38/20	38mm x 2M	10	
TS38/60	38mm x 2M	30	
TS38/100	38mm x 2M	50	
TS38/250	38mm x 2M	125	
TS510	54mm x 100mm	100	1
TS520	54mm x 200mm	50	1
TS54/10	54mm x 1M	10	1
TS54/20	54mm x 2M	10	
TS54/60	54mm x 2M	30	
TS54/100	54mm x 2M	50	
TS54/250	554mm x 2M	125	
TS810	80mm x 100mm	100	1
TS820	80mm x 200mm	50	$\checkmark$
TS80/10	80mm x 1M	10	$\checkmark$
TS80/20	80mm x 2M	10	
TS80/60	80mm x 2M	30	
TS80/100	80mm x 2M	50	
TS80/250	80mm x 2M	125	

## **Magnetic Ticket Holders**

Ref	Size (H x W)	Pack	White Card Included
TS210M	25mm x 100mm	100	1
TS220M	25mm x 200mm	50	1
TS25M/10	25mm x 1M	10	1
TS25M/20	25mm x 2M	10	
TS310M	38mm x 100mm	100	✓
TS320M	38mm x 200mm	50	1
TS38M/10	38mm x 1M	10	1
TS38M/20	38mm x 2M	10	
S510M	54mm x 100mm	100	1
S520M	54mm x 200mm	50	1
S54M/10	54mm x 1M	10	1
S54M/20	54mm x 2M	10	
S810M	80mm x 100mm	100	1
TS820M	80mm x 200mm	50	1
S80M/10	80mm x 1M	10	1
rs80M/20	80mm x 2M	10	

For non standard heights, widths or coloured profiles please contact our sales office for a personalised quotation



**Additional White Card Inserts** 

10

Ref	Size (H x W)	Pack
TC210	25mm x 100mm	100
TC220	25mm x 200mm	50
TC250	25mm x 1M	10
TC310	38mm x 100mm	100
TC320	38mm x 200mm	50
TC350	38mm x 1M	10
TC510	54mm x 100mm	100
TC520	54mm x 200mm	50
TC550	54mm x 1M	10
TC810	80mm x 100mm	100
TC820	80mm x 200mm	50
TC850	80mm x 1M	10

