



## SPECIFICATIONS

LCD Type	3.5" Digital TFT LCD
LCD Brightness	350 cd
Display Resolution	320 x 240 Pixels
Display Color	16.7M Color Screen
Touch Screen	Enabled
CPU	Samsung 2440 400 Mhz
FLASH/RAM	32Mb Flash / 64 Mb RAM
Storage Type	SD/MMC Plus Memory Type
Storage Capacity	128Mb, 256Mb, 512Mb, 1Gb ( 2Gb )(4Gb)
Memory Card Slot	Push-in & Push-out
Built-In GPS Module	Sirf III ( SirfstarIII )
Built-In Battery	Rechargeable Lithium-Ion / 720mA
Speaker	8 Ohm, 1 Watt Speaker x 2 ( Stereo )
Installation	Windshield-Suction Mount
O/S	Microsoft WinCE.Net Core Version 4.2
Map Data	Whereis Version 13
Map Upload Type	SD/MMC Plus Memory Card
Storage Temp Range	-20 C to +70 C
Operating Temp Range	0 C to + 45 C
Voice	Voice Prompts
TMC Connection Port	Ear Jack Type 2.50 ( 4 Pin, RS-323 Interface )
Audio Out Jack	Ear Jack 3.5 ( Stereo )
Optional Premium Menu	Audio ( mp3,wav), Video (avi), Photo (bmp,jpg, gif,png.) Slide Show etc.
Setting	Brightness Adjustment, Calibration, Time Clock, Language Setting etc.

\* Specifications and information are correct at time of publication. Specifications are subject to change without prior notice. Whereis® is the registered trademark of Telstra Corporation.

### BARCODE

Model: OZNAV BOOMERANG 3.5" GPS



9 335577 000551

Zylux Distribution Pty. Ltd.

166 Christmas Street, Fairfield, 3078, Victoria

Phone: (03) 9482 2203 Fax: (03) 9482 7711

[www.oznav.com.au](http://www.oznav.com.au)