

**KLIPPON STB 4 MS HT**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-2083  
 www.weidmueller.com



Ideally suited for the energy and process industry and transportation, the Klippon® STB series is the perfect complement to our existing Klippon housing product line. Enclosures of this series comply with international standards such as EN 62208 and EN 60079-0/7 (ATEX).

Features:

- Comes with a standard seal that is resistant to high temperatures (with an extended temperature range of -50°C to +120°C)
- Flexible options when mounting the internal rail
- The seal is protected against compression; this ensures that a permanent and secure seal is maintained.
- Earth stud in housing cover and bottom section
- Lasered welding seams offer improved quality
- Delivered with welded-on mounting to ensure an optimal housing installation

Weidmüller can manufacture and supply this enclosure to match customer specifications, fitted with all necessary terminals and cable glands.

**General ordering data**

Order No.	<a href="#">1025030000</a>
Part designation	KLIPPON STB 4 MS HT
Version	Enclosures, Sheet steel, 250 mm, 120 mm, 250 mm
GTIN (EAN)	4032248745241
Qty.	1 pc(s).

**KLIPPON STB 4 MS HT**

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

**Technical data**

**Earth, enclosure, cover**

Earth, housing, cover      Welded-on M6 x 12 stainless-steel bolts

**Earth, enclosure, internal**

Earth, housing, internal      Welded-on M6 x 16 stainless-steel bolts

**Earthing enclosure, external**

Earth, housing, external      Welded-on M6 x 16 stainless-steel bolts

**Dimensions**

Length	120 mm	Width	250 mm
Height	250 mm	Fixing dimension, width	275 mm
Weight	4,450 g		

**General information**

Fixing dimension, width	275 mm	Material	Sheet steel
Material thickness	1.5 mm	Surface	lacquered
Colour code	RAL 7032	Cover fixing	M5 hexagon stainless-steel slotted screw with 10mm spanner width
Enclosure fixing	Welded-on mounting foot with 8-mm holes	Integral fixing	TAS 20 rail welded to floor
Material	Sheet steel	Material thickness	1.5 mm
Resistance to shocks	10 J version standard	Sealing material	Silicone
Surface	lacquered		

**Cable glands top/bottom**

M 12	32	M 16	21
M 40	3	M 50	2
M 63	2	M20	12
M25	10	M32	8

**cable glands, left**

M 12 (3)	32	M 16 (3)	21
M 20 (3)	12	M 25 (3)	10
M 32 (3)	8	M 40 (3)	3
M 50 (3)	3	M 63 (3)	2

**cable glands, right**

M 12 (2)	32	M 16 (2)	21
M 20 (2)	12	M 25 (2)	10
M 32 (2)	8	M 40 (2)	3
M 50 (2)	2	M 63 (2)	2

**KLIPPON STB 4 MS HT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

**Technical data****horizontal assembly**

WDU 10 / ZDU 10	2x22	WDU 16 / ZDU 16	2x18
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x42	WDU 4 / ZDU 4	2x35
WDU 6 / ZDU 6	2x27		

**vertical assembly**

WDU 10 / ZDU 10 (2)	2x22	WDU 16 / ZDU 16 (2)	2x18
WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	2x42	WDU 4 / ZDU 4 (2)	2x35
WDU 6 / ZDU 6 (2)	2x27		

**Approvals**

Approvals institutes

**Classifications**

eClass 6.0 27-14-91-07