



K4100 & K5100

DESKTOP & PORTABLE PRINTERS



K4100 easy to use printer for the production of barcodes and labels for office or industrial use, shrink tubing, self-laminating cable markers.

K5100 a portable, rugged, easy to use printer for the production of 'on-site - on demand' shelf edge labels, barcodes and labels for office or industrial use, shrink tubing, self-laminating cable markers.



Our recommendations on the use of our products are based on test data believed to be reliable, but we would ask that you conduct your own tests to determine the suitability for your application. Kroy cannot accept any liability, application. Kroy Caminot accept, any liability, direct or consequential for loss or damage caused as a result of our recommendations. Specifications and pricing may change at any time without notice. Subject to product availability. 1994 Kroy (Europe) Ltd. Kroy and DuraType are registered trademarks of Kroy Inc.

KROY°

Kroy (Europe) Limited Worton Grange, Reading, Berkshire RG2 0LZ England Tel +44 (0)118 9865 200 Fax +44 (0)118 9865 205

www.kroyeurope.com e-mail info@kroyeurope.com

Features include...

Thermal transfer printing technology 300 DPI (12 dots per mm) resolution

2 line-16 character per line LCD Prints 6-72pont in one point increments

Up to 6 lines text

Downloadable, scaleable fonts

User memory to store label formats etc

Flash upgradeable firmware,

Real time clock with time & date stamping facility

10 resident barcode symbologies including

Code 39, 128, UPC and EAN

Multi language prompts

Alpha/numeric sequencing

Repeat function up to 999 copies

Built in cutter

Feed control to eliminate supply wastage

Print styles include bold italic, mirror, frame and underline

Rotate feature for landscape or portrait mode.

Vertical and horizontal printing

Audible key clicks

RJ45 serial connection (cable supplied) for connecting to your PC Printer drivers and Kroy Label Design Software (KLDS) Internal battery charger (K5100 only)*

*Note: To charge K5100 batteries in-situ, the AC Adapter must be used

Dimensions:

K4100:241mm (L) x 203mm (D) x 70mm (W) **K5100:**280mm (L) \times 153mm (D) \times 102mm (W)

Electrical Specification: K4100 & K5100:

AC Adapter input 100-250 VAC, 50/60Hz 43W AC Adapter Output: I2DVC, UL, C-UL, CE Meets VDE-B & FCC Part 15 Class B RFI Limits

K5100: Batteries: C-Size rechargeable Nickel-cadmium 2.2A/Hr.

Serial Port:

RS232 9600 — 115200 baud

Printers & Accessories:

K4100 Desk-top Printer includes K4100 printer, AC Adapter, Power cord Serial Cable and User manual

K5100 Portable Printer includes K5100 printer, AC Adapter, Power cord, Serial Cable and User Manual, 6 NiCd Batteries

K4100 Printer kit includes Carrying case, AC adapter, Power cord, Serial cable, User Manual, 3 Tape Supply Cartridges.

K5100 Printer kit includes Carrying case, AC adapter, Power cord, Serial cable, External battery charger, 6 NiCd batteries, User Manual, 3 Tape Supply Cartridges.

> Service Commercial Tel +33 I 48 69 58 I8 Germany Kundendienst Tel +49 2464 907142



