
# **Brand-Rex**

Brand-Rex Part Number

Rev

www.brand-rex.com

# RG 179 PE with Silver Plated Copper Covered Steel Conductor



#### PHYSICAL CHARACTERISTICS

Inner Conductor:

30 AWG, 7/0.102 mm Silver Plated Copper Covered Steel, 0.31 mm Nom Diameter

Diameter:

Min 0.28 mm Max 0.33 mm

Dielectric:

Extruded solid Low Density Polyethylene Natural.

Diameter:

Min 1.63 mm Max 1.70 mm

Outer Conductor:

Single Braid of 38 AWG, 0.102 mm Tin Plated Copper Wire, 90% Min Coverage.

Diameter:

Max 2.13 mm

Jacket:

Extruded PVC Black.

Diameter:

Min 2.41 mm Max 2.67 mm

IVIAX 2

Print Legend:

To be decided

## **ELECTRICAL CHARACTERISTICS**

Impedance:

75 Ohms Nom

Attenuation:

69 dB/100 m at 400 MHz

Capacitance:

68.8 pF/m Nom

Conductor DCR:

802 Ohm/km Max at 20°C

### GENERAL INFORMATION

Operating Temperature Range:

0°C to +70°C

Weight:

11.5 kg/km Nom

Rohs Compliance:

Yes

Datasheet No.		L6455	© Brand-Rex Limited	Additional Details		
Rev	Date	Initials	Amendment	DFE 6415		
1	3/5/07	DJ	Initial Issue			
$\neg \neg$				Action	Name	Date
		<del></del>	1	Issued By	D. Jukes.	3/5/07
				Reviewed By	M. Chorlton,	3/5/07

Headquarters and Registered Offices

Viewfield Industrial Estate, Glenrothes, Fife, KY6 2RS, Scotland Tel: +44 (0) 1592 772124 Fax: +44 (0) 1592 775314 West Bridgewafer Street, Leigh, Lancashire, WN7 4HB, England Tel: +44 (0) 1942 265500 Fax: +44 (0) 1942 265576

This drawing is the exclusive property of Brand-Rex Limited and must not be copied or reproduced in any way whatsoever without the express consent in writing of Brand-Rex Limited. The drawing is to be used only for the purpose for which it is supplied and must be returned on demand. The contents of the drawing must moreover be treated as strictly confidential and must not be disclosed to any third party without the express consent in writing of Brand-Rex Limited.