



Test Products International, Inc.
The Value Leader™
 800.368.5719



[Home](#)

[Products](#)

[Message Board](#)

[FAQ](#)

[Corporate Story](#)

770 Carbon Monoxide Monitor



FEATURES

- Measure CO from 0 to 999 ppm
- Displays the max. CO reading in PPM since power on
- Displays in hours and minutes, time elapsed since power on
- Displays user set value of audible and visual alarm
- The audible alarm can be switched on and off by pressing the SEL button

SPECIFICATIONS

Size	38.5 mm x 152.0 mm x 70.0 mm
Weight	181.5 g
Sensor	2 year life Electrochemica
Range	0 to 999 ppm
Accuracy	±3 ppm or 5% whichever is greater
Temperature	32°F to 104°F (0°C to 40°C)

Batteries	2 x 1.5v size AA Alkaline
Operating Time	300 hours