

17" TFT Widescreen Black/Silver Multimedia HW173AB



LCD Panel:

- Display size: 17" (43,18 cm) WIDE
- Panel Type: Active Matrix TFT
- Brightness: 250 cd/m² (typ.)
- Contrast: 500:1 (typ.)
- Pixel pitch: 0.255(H)*0.255(V) mm
- Resolution (H x V): WXGA+ 1440 x 900
- Response time: 8 ms (typ.)
- View angles: LR,UD H/V 140°/130°
- Display colours: 16.2M Colours
- Colour: 9300K, 6500K, User Mode
- Display Surface: Anti-Glare

Power:

- Supply: AC 100~240V, 50~60Hz
- Consumption: 28 W

Physical:

- Input 1: D-Sub
- Dimension (W*D*H): 405 x 199 x 317 mm
- Tilt: 0° ~ 20°
- Kensington Lock
- VESA mounting: VESA Standard, 100mm

Controls:

- Front control: Auto, Vol(-), Power/LED, Vol(+), Menu
- On screen display: EN, TC, DE, FR, ES, IT, PT, NL, SC, JS, KR

Certification Safety:

- UL/CUL, TUV, CB, BSMI, FCC, CE, GOST
- Emission: MPR II
- Power saving: EPA Energy Star

Accessories:

- Powercord, VGA cable, users manual (CD), quickstart guide (paper), warranty card