



TENMA®

72-8730 PRODUCT SPECIFICATIONS

Technical Specifications	
Temperature Range	-18°C ~ 280°C
High Measurement Precision	±2°C or 2% (Condition 23°C ± 2°C)
Repeat Precision	< ±0.5°C / <±0.5%
Resolution	0.1
D:S (Distance to Spot Size)	10 to 1
Response Time	500mS
Emissivity	0.95
°C / °F Selection	✓
Laser Switch	✓
Display Backlight	✓
Max Measurement	✓
Min Measurement	✓
Sleep Mode	✓
Low Battery Display	✓
GENERAL CHARACTERISTICS	
Power	9V Battery (6F22)
LCD Size	22 × 22mm
Product Net Weight	185g
Product Size	145 × 80 × 40mm
Standard Accessories	Battery, English Manual
Standard Individual Packing	Blister
Standard Quantity Per Carton	40pcs
Standard Carton Measurement	530 × 485 × 320mm (0.082 CBM Per Standard Carton)
Standard Carton Gross Weight	10kg

*Available at Extra Cost

Specifications and other information are subject to change without further notice