

13 12 11 10 9 8 7 6 70013 4 3 2 1

4 CKT.

6 CKT.  
3 CKT. DUAL  
ROW - ODD

8 CKT.  
4 CKT. DUAL  
ROW - EVEN




12 CKT.  
6 CKT. DUAL  
ROW - EVEN

14 CKT.  
7 CKT. DUAL  
ROW - ODD












16 CKT.  
8 CKT. DUAL  
ROW - EVEN

18 CKT.  
9 CKT. DUAL  
ROW - ODD

20 CKT.  
10 CKT. DUAL  
ROW - EVEN



10 CKT  
SHOWN  
ON SHT 1



J  
I  
H  
G  
F  
E  
D  
C  
B  
A

J  
H  
G  
F  
D  
C  
B  
A

22 CKT.

11 CKT. DUAL  
ROW - ODD

24 CKT.

12 CKT. DUAL  
ROW - EVEN

26 CKT.











13 CKT. DUAL  
ROW - ODD

28 CKT.

14 CKT. DUAL  
ROW - EVEN

30 CKT.

15 CKT. DUAL  
ROW - ODD



32 CKT.







16 CKT. DUAL  
ROW - EVEN

34 CKT.

17 CKT. DUAL  
ROW - ODD

36 CKT.

18 CKT. DUAL  
ROW - EVEN



MFG. SH.	REV.	LTR.	REVISIONS
L3			SEE SHEET 1
L			SEE SHEET 1
L			SEE SHEET 1
K			SEE SHEET 1
J			SEE SHEET 1

70013

REVISIONS ONLY ON CAD SYSTEM

DUAL ROW INTERIM CLIP  
100 GRILL

MOLEX INCORPORATED

U.S.A.

3 PLACE ± .010  
2 PLACE ± .015  
1 PLACE --- ± .030

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DRG. NO. 69532

DATE 2 0 10

BY JUB

CHK'D. DE

SCALE 2:1

FILE NAME 70013-001-1034

DATE 2 0 10

13 12 11 10 9 8 7 6 5 4 3 2 1