





	13	12	11	10	9	8	7	6	5	4	3	2	1			
J	PLATING: 50 M.I. SELECT GOLD (SEE NOTE 2 OPTION 'GS3')			PLATING: 50 M.I. SELECT GOLD (SEE NOTE 2 OPTION 'GS3')			PLATING: 50 M.I. SELECT GOLD (SEE NOTE 2 OPTION 'GS3')			PLATING: 50 M.I. SELECT GOLD (SEE NOTE 2 OPTION 'GS3')						
	DRAINS: WITHOUT DRAIN HOLES			DRAINS: WITHOUT DRAIN HOLES			DRAINS: WITH DRAIN HOLES			DRAINS: WITH DRAIN HOLES						
	PEGS: WITH PEGS			PEGS: WITH PEGS			PEGS: WITH PEGS			PEGS: WITH PEGS						
	MAT'L: 94V-2 [NATURAL]			MAT'L: 94V-0 [NATURAL]			MAT'L: 94V-2 [NATURAL]			MAT'L: 94V-0 [NATURAL]						
	PACKAGING: TRAY PER PK-42440-001			PACKAGING: TRAY PER PK-42440-001			PACKAGING: TRAY PER PK-42440-001			PACKAGING: TRAY PER PK-42440-001						
I	PART NO.	ENG NO.		CKTS	PART NO.	ENG NO.		CKTS	PART NO.	ENG NO.		CKTS	PART NO.	ENG NO.		CKTS
	NO EDP	A-42440-0213	-	2	NO EDP	A-42440-0223	-	2	NO EDP	A-42440-0233	-	2	NO EDP	A-42440-0243	-	2
	NO EDP	A-42440-0413	-	4	NO EDP	A-42440-0423	-	4	NO EDP	A-42440-0433	-	4	NO EDP	A-42440-0443	-	4
	NO EDP	A-42440-0613	-	6	NO EDP	A-42440-0623	-	6	NO EDP	A-42440-0633	-	6	NO EDP	A-42440-0643	-	6
	NO EDP	A-42440-0813	-	8	NO EDP	A-42440-0823	-	8	NO EDP	A-42440-0833	-	8	NO EDP	A-42440-0843	-	8
	NO EDP	A-42440-1013	-	10	NO EDP	A-42440-1023	-	10	NO EDP	A-42440-1033	-	10	NO EDP	A-42440-1043	-	10
	NO EDP	A-42440-1213	-	12	NO EDP	A-42440-1223	-	12	NO EDP	A-42440-1233	-	12	NO EDP	A-42440-1243	-	12
	NO EDP	A-42440-1413	-	14	NO EDP	A-42440-1423	-	14	NO EDP	A-42440-1433	-	14	NO EDP	A-42440-1443	-	14
	NO EDP	A-42440-1613	-	16	NO EDP	A-42440-1623	-	16	NO EDP	A-42440-1633	-	16	NO EDP	A-42440-1643	-	16
H	NO EDP	A-42440-1813	-	18	NO EDP	A-42440-1823	-	18	NO EDP	A-42440-1833	-	18	NO EDP	A-42440-1843	-	18
	NO EDP	A-42440-2013	-	20	NO EDP	A-42440-2023	-	20	NO EDP	A-42440-2033	-	20	NO EDP	A-42440-2043	-	20
	NO EDP	A-42440-2213	-	22	NO EDP	A-42440-2223	-	22	NO EDP	A-42440-2233	-	22	NO EDP	A-42440-2243	-	22
	NO EDP	A-42440-2413	-	24	NO EDP	A-42440-2423	-	24	NO EDP	A-42440-2433	-	24	NO EDP	A-42440-2443	-	24
	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
G	PLATING:			PLATING:			PLATING:			PLATING:						
	DRAINS:			DRAINS:			DRAINS:			DRAINS:						
	PEGS:			PEGS:			PEGS:			PEGS:						
	MAT'L:			MAT'L:			MAT'L:			MAT'L:						
	PACKAGING:			PACKAGING:			PACKAGING:			PACKAGING:						
F	ITEM NO.			CKTS	ITEM NO.			CKTS	ITEM NO.			CKTS	ITEM NO.			CKTS
	-	-	-	2	-	-	-	2	-	-	-	2	-	-	-	2
	-	-	-	4	-	-	-	4	-	-	-	4	-	-	-	4
	-	-	-	6	-	-	-	6	-	-	-	6	-	-	-	6
	-	-	-	8	-	-	-	8	-	-	-	8	-	-	-	8
	-	-	-	10	-	-	-	10	-	-	-	10	-	-	-	10
	-	-	-	12	-	-	-	12	-	-	-	12	-	-	-	12
E	-	-	-	14	-	-	-	14	-	-	-	14	-	-	-	14
	-	-	-	16	-	-	-	16	-	-	-	16	-	-	-	16
	-	-	-	18	-	-	-	18	-	-	-	18	-	-	-	18
	-	-	-	20	-	-	-	20	-	-	-	20	-	-	-	20
	-	-	-	22	-	-	-	22	-	-	-	22	-	-	-	22
	-	-	-	24	-	-	-	24	-	-	-	24	-	-	-	24
D																

STANDARDIZE NOTES FCC NO: UCP2007-2152 DRW: NLSCHM1 DT 2007/03/12 CHKD: ADERR 2007/03/19 APPR: FSM TH 2007/03/19 REVISIONS	QUALITY SYMBOLS  	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>2 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> </table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± ---	1 PLACE	± ---	± ---	DIMENSION STYLE IN/MM	SCALE ---	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		mm	INCH																		
	4 PLACES	± ---	± ---																		
	3 PLACES	± ---	± ---																		
2 PLACES	± ---	± ---																			
1 PLACE	± ---	± ---																			
DRAWN BY ERH	DATE 2000/02/23	CHECKED BY MB	DATE 2000/02/23	APPROVED BY RE	DATE 2000/02/23	TITLE MINI-FIT B.M.I. VERTICAL HEADER ASSY WITH DRAIN HOLE OPTION															
MATERIAL NO. SEE CHART	DOCUMENT NO. SDA-42440-****	 MOLEX INCORPORATED	SHEET NO. 5 OF 6	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																					

