



(8.00-0.28)
015-0.5

CKT.	DIM. "A"	DIM. "B"	DIM. "C"	
06	(1.68)	(5.08)	(1.68)	
08	(1.68)	(7.62)	(1.68)	
10	(1.68)	(10.16)	(4.22)	
12	(1.68)	(12.70)	(4.22)	
14	(1.68)	(15.24)	(6.76)	
16	(1.68)	(17.78)	(6.76)	
18	(1.68)	(20.32)	(9.30)	
20	(1.68)	(22.86)	(1.68)	(19.46)
22	(1.68)	(25.40)	(1.68)	(22.00)
24	(1.68)	(27.94)	(1.68)	(24.54)
26	(1.68)	(30.48)	(1.68)	(27.08)
28	(1.68)	(33.02)	(1.68)	(29.62)
30	(1.68)	(35.56)	(1.68)	(32.16)
32	(1.68)	(38.10)	(1.68)	(34.70)
34	(1.68)	(40.64)	(1.68)	(37.24)
36	(1.68)	(43.18)	(1.68)	(39.78)
38	(1.68)	(45.72)	(1.68)	(42.32)
40	(1.68)	(48.26)	(1.68)	(44.86)
42	(1.68)	(50.80)	(1.68)	(47.40)
44	(1.68)	(53.34)	(1.68)	(49.94)
46	(1.68)	(55.88)	(1.68)	(52.48)
48	(1.68)	(58.42)	(1.68)	(55.02)
50	(1.68)	(60.96)	(1.68)	(57.56)
52	(1.68)	(63.50)	(1.68)	(60.10)
54	(1.68)	(66.04)	(1.68)	(62.64)
56	(1.68)	(68.58)	(1.68)	(65.18)
58	(1.68)	(71.12)	(1.68)	(67.72)
60	(1.68)	(73.66)	(1.68)	(70.26)
62	(1.68)	(76.20)	(1.68)	(72.80)
64	(1.68)	(78.74)	(1.68)	(75.34)
66	(1.68)	(81.28)	(1.68)	(77.88)
68	(1.68)	(83.82)	(1.68)	(80.42)
70	(1.68)	(86.36)	(1.68)	(82.96)
72	(1.68)	(88.90)	(1.68)	(85.50)

15p 12p

Rbt

15p 12p

