

	PART NO.	REVISIONS								
	2226A-03	ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
		-	А	RELEASED	Veena	02/8/08	Suresh	02/8/08	G. C	17/8/08





Specifications:

Current rating Voltage rating Maximum contact resistance Minimum insulation resistance Withstanding voltage Operating temperature rating Material and Finish: Insulator Insulator colour Contact Finish

: 3.0A ac/dc. : 250V ac/dc.

: 20mΩ.

: 1000MΩ.

: 600V ac for one minute.

: -40°C to +105°C.

: High temperature plastic.

: Black.


: Phosphor bronze.

: Gold plated.

Specification Table

Number of Positions	Α	В	Part Number		
3	5.08	7.62	2226A-03		
Dimensions : Millimetres					

Part Number Explanation:



Number of Positions

: 03 = 3 Positions.

(the Group) of are incensed to it. No licence is granted for the use of their man for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The information is subject to change with- out notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or ornision from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the prod- ucts for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or or	TOLERANCES:	DRAWN BY:	DATE:	DRAWING TITLE:			
	UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	Veena	02/08/08]	Single Row Housing &	Terminal - 3 Way	
		CHECKED BY:	DATE:	SIZE DWG NO.	M10001506	ELECTRONIC FILE	REV
		Suresh	02/08/08			2226A-XX-F4(PC0006)_2_DWG	A
		APPROVED BY:	DATE:				
		G.Cook	17/08/08	SCALE: NTS	U.O.M.: mm	SHEET: 1 OI	F 1

http://www.farnell.com

http://www.newark.com

http://www.cpc.co.uk