

Swaged Tip Type K Thermocouple Probes with Fitted Plug



Swaged Tip Sensors with Plug Termination

- Combines quick thermal response with rugged construction
- Suit flowing fluids, H & V applications, process plant
- All stainless steel probe 200 x 6.00mm swaged down to 50 x 3mm with standard plug or 200 x 3mm swaged down to 50 x 2mm with mini plug
- Type K thermocouple sensor

Probe Type	Farnell Code	Labfacility Stock Code
3.0mm, mini plug	163-3448	011049TD
6.0mm, standard plug	163-3449	011050TD

Data Ref; FAR74