


- 1.CABLE:10 PCS NO UL.28AWG(7/0.127),TINNED AND STRANDED COPPER WIRE  
JACKET:PVC,COMPLIANCE ROHS
- 2.1PCS CONNECTOR=0-SUB 9 WAYS FEMALE SOLDER TYPE CONNECTOR  
INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE  
CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED  
SHELL:NICKEL PLATED.  
CONNECTOR COMPLIANCE ROHS
- 3.1PCS CONNECTOR=0-SUB 25 WAYS MALE SOLDER TYPE CONNECTOR  
INSULATOR:P.B.T.+GLASS FIBER,COLOR:BLUE  
CONTACT:COPPER ALLOY,GOLD FLASH OVER NICKEL PLATED  
SHELL :NICKEL PLATED.  
CONNECTOR COMPLIANCE ROHS
- 4.2PCS 5\*6 NUTS, COMPLIANCE ROHS
- 5.HOOD:PVC MOLDED TYPE ON INNER MOLD AND INJECTION  
OUTER MOLD WITH THUMB SCREW#4-22 UNC  
COLOR:BEIGE,COMPLIANCE ROHS
- 6.Fulfill ROHS Guideline
- 7.ELECTRONIC TEST  
100% OPEN SHORT+MISS WIRE TEST

HEAT SEALED



DRAWING

DB9PIN JACK(J1)	WIRE	DB25PIN MALE(P1)
1	—————	8
2	—————	3
3	—————	2
4	—————	20
5	—————	7
6	—————	6
7	—————	4
8	—————	5
9	—————	22
SHELL	—————	SHELL

PART NO   1052	SHEET NO   1	THIRD ANGLE PROJECTION	
TITLE: ADAPTER DB9 PIN FEMALE TO DB25 PIN MALE BEIGE COLOR		SCALE   N.T.S	DRAWN BY & DATE
		SIZE   A4	CHECKED BY & DATE
DWN NO		UNIT	APPROVED BY & DATE
		<input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	