






Adjustable Wrench




98 07 250
tool chrome plated, handle plastic dipped insulated



- Description
- parallel smooth gripping jaws
- continuously variable gripping width
- with scaling for presetting the width apart from the workpiece
- Chrome Vanadium steel

No.	EAN 4003773-	tool	Handle	 mm	 Inch	Jaw width mm	Head width mm	Width mm	Depth mm	 mm	 g
98 07 250 	071518	chrome plated	plastic dipped insulated	30	1 1/8	8,0	16.00	73,0	20,0	260	500

 New
technical change and errors excepted