

Cable Cutters, (ratchet action)

with telescopic handles



95 32 060

head burnished, handles with multi-component grips



- Description







- for copper and aluminium cables, single and multiple wire - also with hard rubber or plastic sheath
- not suitable for steel wire and wire ropes
- also suitable for cables with iron sheath reinforcement
- little handforce required for cutting due to optimum transmission ratio
- high cutting capacity due to two-hand operation and ratchet action
- the blade can be opened in any cutting position
- handle length with multiple position adjustment from 400 - 600 mm (short transport length, individual adaptation to working conditions)
- Blade: special-quality high-grade tool steel, oil-hardened
- handles: high-strength oval aluminium tubing

Model 95 32 060 :

- tool length: 630 - 830 mm
- weight only approx. 3820 g

Model 95 32 100 :

- tool length: 680 - 880 mm
- weight only 4980 g

No.	EAN 4003773-	 Ø mm	 mm ²	MCM	 mm	 g
95 32 060 	071563	60.00	740.00	1400	630	3820
95 32 100 	071570	100.00	960.00	1900	680	4980

 New**Spare Parts (2)**

No.	EAN	
95 39 720	4003773025290	Movable spare blade for 95 31 720 / 95 32 060
95 39 870	4003773025306	Movable spare blade for 95 31 870 / 95 32 100

technical change and errors excepted