




ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

REVISIONS				DOC. NO.	SPC-F005	*	Effective: 7/8/02	*	DCP No: 1398
DCP #	REV	DESCRIPTION		DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
				VEE	19-10-10	JAG	19-10-10	XXX	02-11-10



Notes:

- Material : C1008 Steel
- Plating : Bright nickel chrome
- Ring Diameter : 1.6mm
- Rib Diameter : 1.6mm

Part Number Table

Description	Part Number
Wire Fan Guard	MC32807

Dimensions : Inches (mm)

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:	DRAWING TITLE:			
VEE	19-10-10	Wire Fan Guard			
CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	
JAG	19-10-10	A	MC32807	56P3003	REV
APPROVED BY:	DATE:	SCALE:	NTS	U.O.M.: Millimeters	SHEET: 1 OF 1
XXX	02-11-10				