

Catalogues

Product card: FTB



Sample photo

Including: Base, cover, FEM membrane cable gland for incoming cable, 2 pcs outgoing cable grommets and 1 exit bend guide.

Product nbr:	6916000
Description:	Fiber termination box, PC
Remarks:	Snap-Lock cover
Package:	1
Unit:	PCS
Product group:	FTTH
EAN:	6418074062482
Electric No. Denmark:	8212050015
Electric No. Sweden:	5061750

Dimensions:

Length (mm):	130
Width (mm):	190
Height (mm):	45
Length (inch):	5.1
Width (inch):	7.4
Height (inch):	1.7

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035
Cover colour:	RAL 7035
Gasket material:	EPDM

Temperatures:

Min temperature °C (short term):	-40
Max temperature °C (short term):	120
Min temperature °C (continuous):	-40
Max temperature °C (continuous):	80
Min temperature °F (short term):	-40
Max temperature °F (short term):	250
Min temperature °F (continuous):	-40
Max temperature °F (continuous):	175

Rating:

Ingress Protection (EN 60529):	IP 54
Impact Resistance (EN 50102):	IK 08
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	Yes
UV resistance:	UL 508
Flammability Rating (UL 746 C 5):	UL 94 5V
Glow Wire Test (IEC 695-2-1) °C:	960
NEMA Class:	NEMA 1, 2, 3R,5, 12, 12K, 13

Product is connected to following catalogs:

Fibox Enclosures : FTTH : FTB

COPYRIGHT 
LEGAL NOTICE