



Sample photo

Order symbol: MCE PC 42 MF/M
Product nbr: 7214181

Description: DIN rail modular enclosure, PC
Remarks:

EAN: 6418074007643
El. number:
Finland 3422210
Denmark 8212029046
Italy 7740420

Including: Modular component enclosure with TPE gaskets, mounted DIN 35-rails, wall mount cover plugs and mounting instructions. PC/FEM only: three mounted PEN 10 mm² bars, Multi-FEM and FEM membrane cable glands, module marking stripes and pockets.

Dimensions:		L	W	H	Rating:
mm:		580	306	145	Ingress Protection (EN 60529): IP 65
inch:		22.8	12	5.7	Impact Resistance (EN 50102): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		PC			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			UL Type: UL TYPE 1
Gasket material:		TPE			Certificates:
Temperatures:					Fimko
Short term:		-40 ... 120 °C			Europe EN 50298 1998
Continuous:		-40 ... 80 °C			Gost R
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
PEN 16x10		PEN-bar for MCE 14			
PEN 35x10		PEN-bar for MCE 28+			
PEN H 26140		PEN-bar holder for MCE 14+			
MCE 14 PEN SET		Mounting ready PE/N/PEN -rail set			
MCE MU PEN SET		Multiadapter set			
MCE 14 MU PEN SET		Mounting ready PE/N/PEN -rail set			
FP 26128		Fastening lug set			
FP 26127		Fastening lug set			
FP A 26133		Front plate			
MR 26065		Key lock set			

