

Metal Working Tools - Small Angle Grinders - D28135 in a kitbox. 1400W 125mm

D28135K



D28135K Features

- Dust ejection system removes majority of debris from the air which passes over the motor, preventing abrasion and tracking
- Anti vibration side handle to improve user comfort
- New guard design allows guard fitment, adjustment or removal without the use of tools, for increased flexibility
- Fully leaded stator windings for increased motor durability
- Pop off brushes protect the armature from damage at the end of brush life resulting in greater motor durability
- The low profile gear case allows access in confined areas
- Abrasion protected motor for increased durability
- Anti lock flange prevents flanges from permanently locking up and locking the disc on
- One piece brush arm prevents brush hang up in extreme conditions
- Side positioned spindle lock gives greater protection to button when using in confined spaces

D28135K Specifications

Specifications	
Specifications	Value
Power Input	1400 Watts
Power Output	680 Watts
No Load Speed	10000 rpm

Max. Disc Diameter	125 mm
Spindle Thread	M14
Weight	2 kg
Length	300 mm
Height	80 mm

D28135K Standard

- Protective keyless guard
- multi-position anti vibration side handle
- Inner and outer disc flanges
- Spanner
- Heavy duty carry case