

EPSON®

EXCEED YOUR VISION



Epson Stylus D92

Everyday printer for great photos and documents

Print documents, web pages and even photos in vivid colours with the Epson Stylus D92. It's quick, easy and also cost-effective, because four individual ink cartridges mean you only replace the colour you use.

It's so easy to bring quality and value to your home printing. Whether you print documents or photos, Epson's latest generation of DURABrite™ Ultra Ink provides laser-like text and glossy photos, and is resistant to water, smudging and fading.

With a print speed of up to 25 pages per minute and a range of software, you can really get the best out of your Epson printer. It's also economical with individual ink cartridges because you only replace the colour you use.

Ideal for all your printing – print everything from laser-like documents to glossy photos with DURABrite™ Ultra Ink

Save money with individual ink cartridges – only replace the colour you use

DURABrite™ Ultra Ink gives you long-lasting prints – your prints are water, smudge and fade resistant

Quality at high speed – print up to 25 pages per minute and at up to 5760 optimised dpi on suitable media

Borderless printing – print your glossy photos borderless up to A4

Fantastic photos every time – Epson PhotoEnhance automatically adjusts colour and contrast for perfect results

Easy image editing and printing – with Epson Creativity Suite software

Better photos – remove red-eye with Epson Easy Photo Print

Key benefits:

- Ideal for printing high-quality documents and photos
- Save money with individual inks – only replace the colour you use
- Superb quality with long-lasting Epson DURABrite™ Ultra Ink
- Easy photo editing and printing with Epson Creativity Suite



Epson Stylus D92

Print technology

Printing method

4-colour inkjet printer, Epson Micro Piezo™ print head

Nozzle configuration

90 nozzles black / 29 x 3 nozzles colour (cyan, magenta, yellow)

Droplet size

4 pl (minimum) with Variable-sized Droplet Technology

Ink system

Epson DURABrite™ Ultra Ink

Print resolution

Up to 5760 x 1440 optimised dpi on suitable media using RPM (Resolution Performance Management)

Print speed

Black text A4

Up to 25 ppm*2

Colour text A4

Up to 13 ppm*2

Photo 10x15 cm

Approx. 89 secs*2

Interface

USB – compatible with the USB 2.0 specification*3

Paper handling

Capacity

80 sheets A4 plain paper

Media size

A4, Letter, Legal, 20x25 cm, 13x18 cm, 10x15 cm, 9x13 cm, 13x20 cm, 102x181 mm, A6, A5, B5, Half Letter, Envelopes: No.10, DL, C6
0 mm top, left, right, bottom via custom settings in printer driver*4

Print margin

Ink cartridges

4 individual ink cartridges

T0711 Black
T0712 Cyan
T0713 Magenta
T0714 Yellow

Electrical specification

Power consumption

Approx. 10 W (stand-alone copying, ISO10561 letter pattern, plain paper – text)

Approx. 1.5 W (sleep mode)

Energy Star Rating

Voltage

AC 220-240 V

Operating systems

Windows 98SE*5 / ME*5 / 2000 / XP / XP-x64 / Vista, Mac OS 10.2.8 or later

Warranty

1 year standard warranty
Optional extension to 3 years subject to availability

General

Dimensions (WxDxH)

435x219x165 mm

Weight

2.8 kg






Noise level

45 dB (according to ISO7779 Pattern with Epson Premium Glossy Photo Paper/Photo RPM mode)

Software

Epson Creativity Suite
Epson Web-To-Page
Epson Easy Photo Print

Supplies

	Black	T0711
	Cyan	T0712
	Magenta	T0713
	Yellow	T0714
	Multipack	T0715



*1 Up to 5760 x 1440 optimised dpi on suitable media using RPM (Resolution Performance Management)

*2 For more information, please visit www.epson-europe.com

*3 USB cable required for PC/Mac use (not supplied in the box)

*4 Otherwise 3mm top, left, right, bottom

*5 Windows 98SE/ME are supported for English only



For further information please contact your local Epson office or visit www.epson-europe.com
Austria 0810/20 01 13 (0,07 €/Min.) Belgium 070/350120 (0.1735 €/Min.) Czech 800/142 052
Denmark 44 50 85 85 Finland 0201 552 091 France 0892 899 999 (0,34 €/min) Germany 01805/23 41 10 (0,14 €/Min.)
Greece 210-8099499 Hungary 06800 147 83 Italy 02-660321 10 (0,12 €/Min.) Luxembourg 900/43010 (0,24 €/mn.)
Middle East +9714 8818934 Netherlands 0900-5050808 (0.05 €/oproep + 0.15 €/Min.) Norway 22 06 42 80
Poland 0-0-800 4911299 (0,16 zł/min.) Portugal 707 222 111 Russia (095) 777-03-55 Slovakia 0850 111 429
South Africa (+2711) 465-9621 Spain 93 582 15 00 Sweden 0771-400135 (Mobilsamtal – 0,99 kr/min,
Lokala samtal – 0,30 kr/min, Utlandssamtal – 0,89 kr/min) Switzerland 0848 448820 (4-8 cent./mn.)
Turkey (0212) 3360303 United Kingdom +44 (0) 1442 261144

Entity carrying out management and coordination pursuant to article 2497 bis of Civil Code: Epson Europe BV

EPSON® is a registered trademark of Seiko EPSON® Corporation. All other product names and other company names used herein are for identification purposes only and may be trademarks or registered trademarks of their respective owners. Errors and omissions excepted, all specifications are subject to change without notice.

EPSON®