




## EWF125 PUR5x034L0200 50

Industrial Connectors:Circular Connectors E-series M12/FIXCON:with screw locking:Angled cable socket with integrally molded lead

Product description	
Description	Angled cable socket, with integrally molded lead, self-securing lock nut
Type	EWF125 PUR5x034L0200 50
Order No.	934 402-220
Other standard types	black housing, cable material PUR,
	cable length 5 m: order no. 934 402-221;
	black housing, cable material PVC,
	cable length 2 m: order no. 934 402-120;
	cable length 5 m: order no. 934 402-121
Type of contact	female
Number of contacts	5
Cable material	PUR
Cable color	black
Cable length	2 m
Conductor size	0.34 mm2
Cable specification	high flexible lead
Standard	IEC 61076-2-101 (Ed. 1)/ IEC 60947-5-2
Housing Color	black
Drawing	



Technical data		
Wire stranding	42 x 0.1	
Rated voltage	60 V AC/DC	
Rated current	4 A	
Material		
Contact material	Cu Sn 6	
Contact surface material	Au	
Contact bearer material	PUR	
Housing material	PUR	

Coupling nut material	Zn Al/Ni
O-Ring	Viton
Environmental conditions	
Protection class (IEC 60529)	IP 68 / IP 69K
Pollution severity	3
Temperature range	-25 °C to +90 °C (UL: +80 °C)
Inflammability class	
Cable	fire resist. IEC 332-2
Contact bearer	complies with 94 HB
Approvals	
UL	UL pending
Packaging unit	
Packaging unit	50 pieces
Scope of delivery and accessories	
Accessories to order separately	protective cap M 12 VS, order no. 734 209-100