









**P.C.B. LAYOUT**



**NOTES:**

1. Rating: 250V 28A  
PITCH: 5.00mm
2. Insulation Withstands Voltage:  
AC 1500 V/MIN
3. Insulation Resistance:  
PA= 500MΩ or more at DC500V
4. Using Temperature Range:  
PA= -40°C~+105°C
5. Screw Torque Value: 4 kgf-cm
6. Suitable Electric Wire: AWG 24~12
7. Undimensioned Tolerances:

|                          |    |   |         |
|--------------------------|----|---|---------|
| —                        | ∩  | ∇ | 0.05/10 |
| ⊥                        | // | ≡ | 0.2/10  |
| PITCH ERROR              |    |   | 0.05/10 |
| UNDIMENSIONED TOLERANCES |    |   | ±0.3    |

| 4    | SOLDER PIN   | 0067B00100  | P               | BRASS    | Ni Plated                |
|------|--------------|-------------|-----------------|----------|--------------------------|
| 3    | WIRE CAGE    | X000002200  | P               | STEEL    |                          |
| 2    | SCREW        | S000011100  | P               | STEEL    | M2.5x0.4                 |
| 1    | HOUSING      | 0067C0XX00  | 1               | PA66(V2) | G002                     |
| ITEM | NAME OF PART | NO. OF PART | Q"TY            | MATERIAL | NOTES                    |
| DWG. | <b>X.JF</b>  | DATE        | <b>03,02,16</b> | UNITS    | MM SHEET/OF <b>1 / 2</b> |
| CHK. |              | DATE        |                 | SCALE    | <b>4:1</b> ( : )         |
| APP. |              | DATE        |                 | NAME     | <b>20.700M</b>           |
|      |              |             |                 | DWG NO.  | <b>SP-02</b>             |

|      |         |      |      |
|------|---------|------|------|
| REV. | CONTENT | CHK. | DATE |
|      |         |      |      |

**IMO**