


ITEM NO	PART NUMBER	DESCRIPTION	QTY / ASSY
1	I-1337427-0	50 Ohm BNC STGHT PLUG - SILVER/SILVER	2
2	I337767-2	STRAIN RELIEF	2
3	I337715-1	RG58C/U CABLE	A/R



2000 ±25	I337771-8
1800 ±25	I337771-7
1500 ±25	I337771-6
1200 ±25	I337771-5
1000 ±25	I337771-4
600 ±15	I337771-3
500 ±12	I337771-2
250 ±10	I337771-1
DIM 'A'	AMP PART NUMBER

P	LTR	DESCRIPTION	DATE	DW
1		FIRST ISSUE	21DEC00	RC

THE DIMENSIONS AND TOLERANCES SHOWN ON THIS DRAWING ARE THE PROPERTY OF TYCO ELECTRONICS CORPORATION. NO PART OF THIS DRAWING IS TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, WITHOUT PERMISSION IN WRITING FROM TYCO ELECTRONICS CORPORATION.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
MM	
0 PLC	± .1
1 PLC	±0.01
2 PLC	±0.001
3 PLC	±0.0001
4 PLC	±0.0001
ANGLES	±
FINISH	

MATERIAL	FINISH

DWG	21DEC2000
CHK	R. CHURCHILL
APPRO	D. CHICK
PRODUCT SPEC	21DEC2000
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

**tyco**  
**Electronics**

AMP of Great Britain Ltd.,  
 Stanmore, Middlesex, HA7 8R

NAME: BNC PLUG - BNC PLUG CABLE ASSEMBLY

SIZE: A3  
 CAGE CODE: 00779  
 DRAWING NO: G=1337771

SCALE: NTS

SHEET 1 OF 1