

今入企業股份有限公司

JIN RUH CO., LTD.

No. 12, Lane 55, Sec. 4, Hi Dien Road, Tainan, Taiwan

Tel: 886-6-2552136~8, Fax: 886-6-2565664, 2472585

E-mail: jin.ruh@msa.hinet.net

PRODUCT TEST REPORT			
品名 TYPE OF SWITCH	I.D.2.1mm DC Chassis Jack	型号 MODEL NO	JR 1821
一、构造 CONSTRUCTION	(一)、形状、尺寸依照图面规定 SHAPE AND DIMENSIONS SUBJECT TO ATTACHED CHART REGULATION		
	(二)、外观 无电镀不良、破损、裂痕等现象 APPEARANCE: EVERY PART SHOULD BE FINISHED NOT TO DILAPIDATION.FLAW.CRACK AND BAD PLATING		
二、机械性能 MECHANICAL STRUCTURE	插拔力 300g To 800g INSERTION EXTRACTION FORCE: 300g To 800g		
三、电气特性 ELECTRICAL CHARACTERISTIC	(一)、接触阻抗 (CONTACT RESISTANCE): 内导体之间(CENTER CONTACT) $\leq 10 \text{ m}\Omega$ 外导体之间(OUTER CONTACT) $\leq 2.5 \text{ m}\Omega$		
	(二)、绝缘阻抗(INSULATION RESISTANCE): 内导体之间(CENTER CONTACT) $\geq 100 \text{ m}\Omega$ 外导体之间(OUTER CONTACT) $\geq 200 \text{ m}\Omega$		
	(三)、耐压(WITHSTAND VOLTAGE): 1000V rms(海平面有效值)		
	(四)、额定电流(CURRENT RATING): AC: 5A/ 500V DC: 5A/250V		
	(五)、工作温度(OPERATING TEMP RANGE): -40 ~ +60°C		
	(六)、电压驻波比(VSWR): 直式(STRAIGHT) ≥ 1.20 弯式(RIGHT ANGLE) ≥ 1.30		
四、电气寿命 ELECTRICAL DURABILITY	插拔 (耐用性) 5000 次(Cycles) 5000 TIMES INSERTING & EXTRACTING AT FULL LOAD		