


P/N	MATERIAL	COLOR
WITBH-50R	NYLON 6/6, UL94 V-2 (RMS-01)	NATURAL
WITBH-50R-HS	HEAT STABILIZED NYLON 6/6, UL94 V-2 (RMS-47)	BLACK



NOTES:  
 1. TO PRESS-FIT INTO A .250+/- .003 (6.35+/- .08) HOLE @ .25 (6.35) MIN THICKNESS

TITLE: WIT-50 WITH BLIND HOLE FIX		DWG IN IN [MM]		FINAL	
CREATED USING SOLIDWORKS	FILE #: WITBH-50	DWN: D.J.Z.	APP: D.J.Z.	PART #	
TOLERANCES UNLESS NOTED .XX=±.01 .XXX=±.005 .XXXX=±.0020 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: A	DT: 08/01/2007	CHKD: SJ	PRINT TYPE
RE: RICHCO INC. --	RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		WITBH-50R		CA
A	RELEASED FOR PRODUCTION	SK	10/11/07		
REV.	DESCRIPTION	ENGR.	DATE		