

4

This L26 connector uses a "sliding" contact technology suitable : 5000 MΩ min Α : 750 Vrms min : $100 \,\mathrm{max}$: Normally closed Housing : PBT 30 % Glass Filled, Colour Black, Rated UL94V0 В Gold on contact area : see catalogue part number key Matte Tin 3µm mini on solder tail in place of Tin/Lead C General tolerances: \pm 0.2 mm tolerance projection mm ISO 406 $\oplus \in$ ISO ||0| 5S2F size Scale D Α3 SEE NOTES 3:2 SEE NOTES ECN 105-0071 Rev. VJ₩_54704 ٩g В SEE TABLE CUSTOMER COPY sheet | of 2

