



WD Scorpio® Blue™ 2.5-inch Hard Drives

Massive Capacity
Low Power Consumption
Ultra-cool and Quiet



Big Capacity for Portable Computing.

WD Scorpio Blue 5400 RPM 2.5-inch SATA and EIDE hard drives from Western Digital deliver lightning-fast and ultra-quiet performance hand-in-hand with low power consumption. In addition, these hard drives are designed with ruggedness, reliability, and data-protection features that actively watch over valuable data. Capacities range from 40 to 320 GB.



Ideal for portable digital devices of all kinds, including notebook computers, external storage, and digital media players.



- **Massive capacity** – Whether they are in an external drive or a notebook computer, 320 GB WD Scorpio Blue 2.5-inch drives offer the most available capacity for space-hungry operating systems like Windows Vista™, plus plenty of room left over for photos, music, and video.
- **Quiet** – In a notebook drive, silence is golden. WD's exclusive WhisperDrive™ combines state-of-the-art seeking algorithms to yield one of the quietest 2.5-inch hard drives on the market. These algorithms also optimize the way a drive seeks for data, which significantly improves power consumption. So now silence (and longer battery life) is golden.
- **Reliable and Rugged** – WD's ShockGuard™ technology protects the drive mechanics and platter surfaces from shocks. WD's SecurePark™ parks the recording heads off the disk surface during spin up, spin down and when the drive is off. This ensures the recording head never touches the disk surface resulting in improved long term reliability due to less head wear, and improved non-operational shock tolerance.



PUT YOUR LIFE ON IT®



WD Scorpio Blue 2.5-inch Hard Drives

Capacities and Models

	SATA	EIDE
320 GB	WD3200BEVT	
250 GB	WD2500BEVS	WD2500BEVE
160 GB	WD1600BEVS	WD1600BEVE
120 GB	WD1200BEVS	WD1200BEVE
80 GB	WD800BEVS	WD800BEVE
60 GB	WD600BEVS	WD600BEVE
40 GB	WD400BEVS	

Key Specifications

Interface:	SATA or EIDE
Form Factor:	2.5-inch
Spin Speed:	5400 RPM
Cache:	8 MB
Limited Warranty:	3-year

Capacities

40 GB – 320 GB

Featuring WD's Exclusive Intelligent Drive Technology

- **Fast and efficient** – With 5400 RPM spin speed 12 ms access time, and up to 3 Gb/s SATA interface speed, even the most demanding customer will appreciate the performance achieved by WD Scorpio Blue drives.
- **Tested for Compatibility** – We perform tests on hundreds of systems and a multitude of platforms in our FIT Lab™ and Mobile Compatibility Lab to give our customers confidence that WD drives will work in their systems.

WD Scorpio Blue is part of WD's complete lineup of mobile hard drives.

 <p>WD Scorpio® Black™ Maximum performance for power computing.</p>	 <p>WD Scorpio® Blue™ Big capacity for portable computing.</p>
--	--



Western Digital, WD, the WD logo, WD Scorpio, and Put Your Life On It are registered trademarks; Black, Blue, SecurePark, ShockGuard, Fit Lab, and WhisperDrive are trademarks of Western Digital Technologies, Inc. Other marks may be mentioned herein that belong to other companies. Picture shown may vary from actual product. Product specifications subject to change without notice. © 2008 Western Digital Technologies, Inc. All rights reserved.

One gigabyte (GB) = one billion bytes. Total accessible capacity varies depending on operating environment.

2178-001036-A09 June 2008