

Western Digital

WD My Book 1TB AV DVR Expander WDBABT0010HBK - Hard drive - Hi-Speed USB / eSATA-30

Overview

Product Description

Western Digital My Book AV 1TB eSATA USB DVR Expander (External).

Expand your DVR storage so you can record more of your favorite TV shows. Or, transfer and store videos from your compatible camcorder to free up space for more recording. Connect the drive to a game console, Blu-ray Disc player or media player, like one from the WD TV family, to smoothly stream video to your big screen TV. It's the perfect solution for your video storage and playback needs.

High-capacity DVR expander

Instantly add more recording hours to your DVR. Connect the drive to your compatible USB or eSATA DVR to instantly create more storage for your TV shows, sporting events, and movies

A convenient storage companion for your camcorder

Transfer your videos to your My Book AV drive without a computer to make room for more recording. You can even use the camcorder to play back the videos stored on the My Book AV drive (see compatibility)

AV-optimized

My Book AV DVR Expander offers smooth video recording and playback with SilkStream technology (available via eSATA connection only). Built with WD GreenPower Technology, the drive inside is optimized for the demands of reading and writing v

Small enough to fit in your entertainment centre

The small My Book form factor fits neatly in your entertainment centre. It can stand upright or lay horizontally, making it easy to neatly position your drive near your AV devices while maximizing airflow

Maximum flexibility

My Book AV has both USB 2.0 and eSATA interfaces so your drive is compatible with most DVRs and other AV devices

Specification

Product Specifications

General

Device Type	Hard drive - external
Width	4.8 cm
Depth	13.5 cm
Height	16.5 cm
Weight	1.18 kg
Localisation	Middle East, Africa, Europe

Hard Drive

Capacity	1 TB
Interface Type	Hi-Speed USB / eSATA-300

Performance

Interface Transfer Rate	3.0 Gbps (eSATA) / 480 Mbps (Hi-Speed USB)
--------------------------------	--

Expansion / Connectivity

Interfaces	1 x eSATA-300 - 7 pin external Serial ATA ¦ 1 x Hi-Speed USB
-------------------	--

Miscellaneous

Included Accessories	Feet for horizontal placement
Cables Included	1 x USB cable - external ¦ 1 x eSATA cable - external
Compliant Standards	RoHS

Environmental Standards

ENERGY STAR Qualified	Yes
------------------------------	-----

Power

Power Source	Included AC adapter
Power Device	Power adapter
Voltage Required	AC 120/230 V (50/60 Hz)

Software / System Requirements

OS Required Apple MacOS X, Microsoft Windows Vista / XP / 7

Manufacturer Warranty

Service & Support 2 years warranty

Service & Support Details Limited warranty - 2 years

Environmental Parameters

Min Operating Temperature 5 °C

Max Operating Temperature 35 °C