

Facom J.10 3/8" Drive OGV Socket 10mm



Description

Higher torque without damage to fasteners !

The OGV® profile is achieved by a succession of curves instead of the flats found in conventional sockets.

More powerful tightening: Larger contact area between socket and fastener minimizes stress.

Less wear: Torque is transmitted through the fastener flats instead of the corners.

Increased durability: Stress concentration in the corners is eliminated.

Technical specification:

10mm AF 12 point socket with 3/8" drive

Performance: to GGG.W.641E, ANSI B 107.1, ASME B 107.1.